

GTR-3

Visible Light T&R Meter

Measure visible light transmittance and reflectance.



Brief

The GTR-3 is used to measure visible transmittance and reflectance for flat materials, such as flat float glass, colored glass, and coated glass. Scattered light cannot be measured. This instrument is not necessarily equipped with a computer, which is economical and easily used.

Functions

Visible light transmittance, Visible light reflectance.

Parameters

Item	Parameters
Geometric conditions	8°/ 8°
Illuminant	CIE standard illuminant A
Observer	CIE1931 V (λ)
Repeatability	0.2%
Accuracy	1%
Sample size	Min:50*50mm, Max: less than 110mm from the edge
Sample thickness	Max: 30mm
Dimension	330*260*500mm
Power supply	100V~240VAC,50/60Hz,3A
Power	60W

Remark: Aoptek reserves the right to modify the information, the actual instrument & manual be as final.